

## APPLICATIONS

- ➤ Low Cost Analog and Digital Data Links
- ➤ Digitized Audio
- ➤ Optical Sensors
- ➤ Medical Instruments
- ➤ Robotics Communications
- ➤ Motor Controller Triggering
- ➤ EMC/EMI signal Isolation
- ➤ Electronic Games
- ➤ Intra-System Links: Board-to-Board, Rack-to-Rack

#### DESCRIPTION

The IF-E91A and IF-E91B are high output medium speed infrared LEDs in a "connector-less" style plastic fiber optic package. The output spectrum peaks at 950 nm for the IF-E91A and 880 nm for the IF-E91B. The device package features an internal micro-lens, and the PBT housing ensures efficient optical coupling into standard 1000  $\mu$ m plastic fiber cable.

## APPLICATION HIGHLIGHTS

The high output and fast transition times of the IF-E91A and IF-E91B make them suitable for low cost analog and digital data links. Used with an IF-D96 photologic detector, the IF-E91A and IF-E91B can achieve data rates of 500 Kbps and 1 Mbps respectively at link distances up to 7 m. The drive circuit design is simpler than required for laser diodes, making the IF-E91A and IF-E91B excellent low cost alternatives in a variety of analog and digital applications.

### **FEATURES**

- ◆ Excellent Linearity
- ◆ No Optical Design Required
- Mates with Standard 1000 μm Core Jacketed Plastic Fiber Cable
- ◆ Internal Micro-Lens for Efficient Coupling
- ◆ Inexpensive Plastic Connector Housing
- ◆ Connector-Less Fiber Termination and Connection
- Interference-Free Transmission from Light-Tight Housing

# MAXIMUM RATINGS

 $(T_{\Delta} = 25^{\circ}C)$ 

Operating and Storage Temperature Range (T <sub>OP</sub> , T <sub>STG</sub> )40° to 85°C
Junction Temperature $(T_J)$ 85°C
Soldering Temperature (2 mm from case bottom) $(T_S)$ t $\leq$ 5 s240° C
Reverse Voltage ( $V_R$ )3 V
Power Dissipation ( $P_{TOT}$ ) $T_A = 25$ °C100 mW
De-rate Above 25°C1.33 mW/°C
Forward Current, DC (I <sub>F</sub> )  IF-E91A50 mA  IF-E91B100 mA
Surge Current ( $I_{FSM}$ ) $t \le 10 \mu sec$ IF-E91A

# CHARACTERISTICS (T<sub>A</sub>=25°C)

Parameter	Symbol	IF-E91A	IF-E91B*	Unit
Peak Wavelength	$\lambda_{ ext{PEAK}}$	950	880	nm
Spectral Bandwidth (50% of I <sub>MAX</sub> )	Δλ	40	80	nm
Output Power Coupled into Plastic Fiber (1 mm core diameter). Distance Lens to Fiber ≤0.1 mm, 10 cm polished fiber, I <sub>F</sub> =20 mA	$\Phi_{ ext{min}}$	>100 -10	>75 -11.2	μW dBm
Switching Times (10% to 90% and 90% to 10%) ( $R_L$ =47 $\Omega$ , $I_F$ =10 mA)	t <sub>r</sub> , t <sub>f</sub>	1.0	0.5	μs
Capacitance	C <sub>0</sub>	25	25	pF
Forward Voltage (I <sub>F</sub> =50 mA)	V <sub>f</sub>	1.5 max	1.7 max	V
Temperature Coefficient, λ <sub>PEAK</sub>	$TC_{\lambda}$	0.3	0.3	nm/K

<sup>\*</sup> IF-E91D recommended for new designs




FIGURE 1. Normalized power launched versus forward current.




FIGURE 2. Typical spectral output vs. wavelength.





FIGURE 3. Cross-section of fiber optic device.

## FIBER TERMINATION INSTRUCTIONS

- 1. Cut off the ends of the optical fiber with a singleedge razor blade or sharp knife. Try to obtain a precise 90-degree angle (square).
- Insert the fiber through the locking nut and into the connector until the core tip seats against the internal micro-lens.
- 3. Screw the connector locking nut down to a snug fit, locking the fiber in place.



#### Notes:

- Y AND Z ARE DATUM DIMENSIONS AND T IS A DATUM SURFACE,
- 2. POSITIONAL TOLERANCE FOR D Ø (2 PL):

  | ⊕ | Ø 0.25(0.010) M | T | Y M | Z M |
- 3. POSITIONAL TOLERANCE FOR F DIM (2 PL):

  (a) 0.25(0.010) (b) T Y (c) Z (d)
- 5. POSITIONAL TOLERANCE FOR Q Ø:
- (♠ Ø 0.25(0.010) (M) | T | Y (M) | Z (M) |
  6. POSITIONAL TOLERANCE FOR B: | (♠ | Ø 0.25(0.010) (M) | T |
- 7. DIMENSIONING AND TOLERANCING PER ANSI Y14,5M, 1982.
- 8. CONTROLLING DIMENSION: INCH

## PACKAGE IDENTIFICATION:

- ◆ E91A-Blue housing w/ Blue dot E91B-Blue housing w/ Green dot
- PIN 1. Cathode
- PIN 2. Anode

	MILLIMETERS		INCHES		
D <b>I</b> M	MIN	MAX	MIN	MAX	
Α	23.24	25.27	.915	.995	
В	8.64	9.14	.340	.360	
С	9.91	10.41	.390	.410	
D	1.52	1.63	.060	.064	
Ε	4.19	4.70	.165	.185	
F	0.43	0.58	.017	.023	
G	2.54 BSC		.100 BSC		
Н	0.43	0.58	.017	.023	
J	7.62 BSC		.300 BSC		
K	10.35	11.87	.408	.468	
L	1.14	1.65	.045	.065	
N	2.54 BSC		.100 BSC		
Q	.305	3.30	.120	.130	
R	10.48	10.99	.413	.433	
S	6,98 BSC		.275 BSC		
U	0.83	1.06	.032	.042	
٧	6.86	7.11	.270	.280	
W	5.08 BSC		.200 BSC		
Х	10.10	10.68	.397	.427	

FIGURE 4. Case outline.