

**AFONICS****LD-0001****1310nm Fabry Perot Laser Diode****Performance Highlights**

- Over 1.5mW into 9/125µm fibre available
- Designed for 1.2Gbit/s data rates
- Multi-Quantum Well (MQW) active layer
- Laser diode electrically isolated from monitor photodiode

LIMITING VALUES	SYMBOL	VALUE	UNITS
Laser diode continuous forward current ⁽¹⁾	$I_{F(LD)}$	$I_{TH} + 40$, DC	mA
Laser diode reverse voltage	$V_{R(LD)}$	2	V
Photodiode continuous forward current	$I_{F(PD)}$	2	mA
Photodiode reverse voltage	$V_{R(PD)}$	20	V
Operating temperature	T_{OPR}	-40 to +85	°C
Storage temperature	T_{STG}	-40 to +100	°C
Soldering temperature 2mm from case for 10s	T_{SLD}	260	°C





OPTICAL/ELECTRICAL CHARACTERISTICS	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITION
Low power option (9/125µm) (50/125µm)	P_F	250 1000			µW	$I_F = I_{OP}$
Medium power option (9/125µm) (50/125µm)	P_F	500 1500			µW	$I_F = I_{OP}$
High power option (9/125µm) ⁽²⁾	P_F	1500			µW	$I_F = I_{OP}$
Threshold current	I_{TH}		5	15	mA	CW
Operating current	I_{OP}		20	45	mA	$I_F = I_{OP}$
Operating voltage	V_{OP}		1.1	1.5	V	$I_F = I_{OP}$
Lasing wavelength	I_P	1290	1310	1330	nm	$I_F = I_{OP}$
Spectral width (rms)	$\Delta\lambda$		1	2	nm	$I_F = I_{OP}$
Rise and fall times (10% to 90%)	t_{LR} / t_{LF}		0.3	0.7	ns	$I_{BIAS} = I_{TH}$, $I_F = I_{OP}$
Monitor current	I_M	0.1	0.5		mA	$I_F = I_{OP}$
Photodiode dark current	$I_{D(PD)}$		0.01	0.1	µA	$V_{R(PD)} = 10V$
Photodiode capacitance	$C_{(PD)}$		10	20	pF	$V_{R(PD)} = 10V$, $f=1MHz$

All values apply at a temperature of 25°C

NOTES:

- 1) Must not be exceeded when operated under pulsed conditions.
- 2) Only available in high power pigtail or minipigtail receptacle option.

Afonics Fibreoptics Ltd. reserves the right to introduce changes without notice. No responsibility is assumed for its use nor for any infringement of the rights of third parties.



NOTE: The device is very susceptible to damage by electrostatic discharge.

NOTES:

- 1) Standard pin orientation aligns pin 2 with the receptacle keyway unless a custom orientation is requested.
- 2) Usable pin length will vary dependant on choice of receptacle. If pin length is important please contact Afonics before placing an order.