


# **Optical Comparator Array** Type OPR5009



### **Features**

- Surface mountable
- TTL compatible output
- · Wide supply voltage range


### Description

The OPR5009 is a hybrid sensor array consisting of three channels of the Optek OPC8031 Differential Optical Comparator, ("DOC-2") IC. Specifically designed for high speed/high resolution encoder applications, the open collector output switches based on the comparison of input photodiode's light current levels. Logarithmic amplification of the input signals makes possible operation over a wide range of light levels.

The packages are surface mountable with two alignment holes, and made from a custom opaque polyimide which shields the active devices from stray light. The high temperature laminate can withstand multiple exposures to the most demanding soldering conditions. Wrap around contacts are gold plated for exceptional storage and wetting characteristics.

### **Absolute Maximum Ratings** (T<sub>A</sub> = 25<sup>o</sup> C unless otherwise noted)

Storage Temperature
Operating temperature
Supply Voltage
Output Voltage
Output Current
Power Dissipation
Soldering Temperature (Vapor Phase Reflow for 30 sec.)



**OPC8031 Block Diagram** 

## **Type OPR5009**

### PRELIMINARY

Electrical Characteristics (T<sub>A</sub> = 25° C unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS	NOTES
Icc	Supply Current		9	20	mA	V <sub>CC</sub> = 24 V	
V <sub>OL</sub>	Low Level Output Voltage		0.3	0.4	V	$I_{OL} = 14 \text{ mA}, V_{CC} = 4.5 \text{ V}$	2
I <sub>OH</sub>	High Level Output Current		0.1	1.0	μΑ	$V_{CC} = V_{O} = 20.0 \text{ V}$	3
OPT-HYS	Optical Hysteresis	2.0	15.0	40	%	$V_{CC} = 5.0 \text{ V}, I_{OL} = 1.0 \text{ mA}$	4, 7
OPT-OFF	Optical Offset	-40	10	+40	%	V <sub>CC</sub> = 5.0 V, I <sub>OL</sub> = 1.0 mA	4, 7
fmax	Frequency Response		1.0		MHz	V <sub>CC</sub> = 5.0 V	5
tlh	Output Rise Time		1.0		μs		6
thl	Output Fall Time		300		ns		

#### Notes:

- 1. Pin (+) = 1.2  $\mu$ W and Pin (-) = 0.8  $\mu$ W.
- 2. Pin (+) = 100.0 nW and Pin (-) = 1.0  $\mu$ W.
- 3. Pin (+) =  $1.0 \mu W$  and Pin (-) 100.0 nW.
- 4. Pin (-) held at 1.0  $\mu$ W while Pin (+) is ramped from 0.5  $\mu$ W to 1.5  $\mu$ W and back to 0.5  $\mu$ W.
- 5. Pin (+) modulated from 1.0 μW to 2.0 μW. Pin (-) modulated from 1.0 μW to 2.0 μW with phase shifted 180<sup>0</sup> with respect to Pin (+). Use 100 kΩ trimpot to set the output signal to 50% duty cycle for maximum operating frequency.
- 6. Measured between 10% and 90% points.
- 7. Optical Hysteresis and Optical Offset are found by placing 1.0 μW of light on the inverting photodiode and ramping the light intensity of the noninverting input from .5 μW up to 1.5 μW and back down. This will produce two trigger points, an upper trigger point and lower trigger point. These points are used to calculate the optical hysteresis and offset.

These are defined as:

% Optical Hysteresis = 100 x (P rise - P fall)

P in (-)

% Optical Offset = 100 x (P average - P (-))

P in (-)


#### Where:

P in (-) = Light level incident upon the "-" photodiode on the I.C. chip (Pin (-) = 1.0  $\mu$ W).

P rise = Value of light power level incident upon the "+" photodiode that is required to switch the digital output when the light level is an increasing level (rising edge).

P fall = Value of light power level incident upon the "+" photodiode that is required to switch the digital output when the light level is a decreasing level (falling edge).

### **Application Circuit**



#### Notes:

- A capacitor of a value between .001 to .01 μF connected as close as possible to the trim terminals is recommended if the device appears to be susceptable to noise transients. These capacitors will reduce f<sub>max</sub>. It is left to the user to determine the best value for the application.
- The 74LS04 is recommended as a means of isolating the "DOC" comparator circuitry from transients induced by inductive and capacitive loads.
- 3. It is recommeded that a decoupling capacitor be placed as close as possible to the device.

Optek reserves the right to make changes at any time in order to improve design and to supply the best product possible.